

Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM
0,74	1,02	FPM 75	7,52	3,53	FPM 75	12,5	1	FPM 75	18,72	2,62	FPM 80	23	3,5	FPM 80
1	1	FPM 75	7,59	2,62	FPM 75	12,5	1,5	FPM 75	18	1	FPM 80	23,16	5,33	FPM 75
1,07	1,27	FPM 75	7,5	1	FPM 75	12,5	2	FPM 75	18,5	1	FPM 80	23,39	3,53	FPM 75
1,24	2,62	FPM 75	7,65	1,63	FPM 75	12,5	3	FPM 75	18,77	1,78	FPM 75	23,47	2,62	FPM 75
1,42	1,52	FPM 75	7,65	1,78	FPM 75	12,5	2	FPM 75	18,72	2,62	FPM 75	23,47	2,95	FPM 75
1,5	1	FPM 75	7,3	2,4	FPM 80	12,5	3	FPM 75	18	5	FPM 75	23,52	1,78	FPM 75
1,5	1,5	FPM 75	7	1,5	FPM 80	13	1	FPM 75	18	1	FPM 75	23,5	3	FPM 80
1,78	1,78	FPM 75	8	1	FPM 75	13	2	FPM 75	18	1,5	FPM 75	23,39	3,53	FPM 90
2	1	FPM 75	8,92	1,83	FPM 90	13	2,5	FPM 75	18	2	FPM 75	23,47	2,62	FPM 75
2	1,5	FPM 75	8	5	FPM 75	13	3	FPM 75	18	2,5	FPM 75	23,39	3,53	FPM 75
2	2	FPM 75	8,5	1	FPM 75	13	4	FPM 75	18	3	FPM 75	23,16	5,33	FPM 75
2,06	2,62	FPM 75	8,5	1,5	FPM 75	13	5	FPM 75	18	4	FPM 75	23	3,5	FPM 80
2,5	1	FPM 75	8	4	FPM 75	13,1	2,62	FPM 75	18,5	2,5	FPM 75	23,3	2,4	FPM 80
2,5	1,5	FPM 75	8	5	FPM 75	13,46	2,08	FPM 75	18,5	2	FPM 75	23	2,5	FPM 75
2,5	2	FPM 75	8,5	1	FPM 75	13,5	2	FPM 75	18,42	5,33	FPM 75	24,5	3	FPM 75
2,57	1,78	FPM 75	8,5	1,5	FPM 75	13,5	2	FPM 75	18,5	1	FPM 75	24,5	3	FPM 80
2,8	1,5	FPM 75	8,5	2	FPM 75	13,5	2,5	FPM 75	18,5	2	FPM 80	24,2	3	FPM 80
2,84	2,62	FPM 75	8,5	2,5	FPM 75	13,5	3	FPM 75	19	4	FPM 75	24,99	3,53	FPM 75
2,9	1,78	FPM 75	8,5	2,5	FPM 75	13,64	5,33	FPM 75	19,18	2,46	FPM 90	24,99	3,53	FPM 90
2,6	1,4	FPM 75	8,73	1,78	FPM 75	13,87	3,53	FPM 75	19,8	3,6	FPM 90	24,77	5,33	FPM 75
2	1	FPM 75	8,92	1,83	FPM 75	13,94	2,62	FPM 75	19,5	3	FPM 80	24,5	3	FPM 75
3	1,5	FPM 75	8,3	2,4	FPM 90	13	2	FPM 90	19	1	FPM 75	24,5	2	FPM 75
3,8	1,9	FPM 75	8,92	1,83	FPM 90	13	2,5	FPM 80	19	1,5	FPM 75	24,2	3	FPM 75
3,68	1,78	FPM 75	8	1,5	FPM 90	13,5	2	FPM 80	19	2	FPM 75	24	3,5	FPM 75
3,63	2,62	FPM 75	9	1	FPM 75	13,87	3,53	FPM 75	19	2,5	FPM 75	24,6	2,4	FPM 80
3,6	2,4	FPM 75	9	1,5	FPM 75	13,94	2,62	FPM 75	19,5	3	FPM 75	24	1,5	FPM 75
3,55	1,8	FPM 75	9	2	FPM 75	14	1	FPM 75	19	3	FPM 75	24	2	FPM 75
3,5	2	FPM 75	9	2,5	FPM 75	14	1,5	FPM 75	19,5	3	FPM 80	24	3	FPM 75
3,5	1,5	FPM 75	9,25	1,78	FPM 75	14	1,78	FPM 75	19	3	FPM 80	24,6	2,4	FPM 80
3,5	1	FPM 75	9,5	1,5	FPM 75	14	2	FPM 75	19	5	FPM 75	24,5	3	FPM 80
3,17	1,78	FPM 75	9,5	2	FPM 75	14,8	2,4	FPM 75	19,99	5,33	FPM 75	25,04	2,95	FPM 75
3	3	FPM 75	9,5	2,5	FPM 75	14,5	2,5	FPM 75	19,5	3	FPM 75	25	1,5	FPM 75
3	2	FPM 75	9,25	1,78	FPM 75	14,5	2	FPM 75	19,5	2,5	FPM 75	25	2	FPM 75
3	1	FPM 75	9,5	1,5	FPM 75	14,5	1,5	FPM 75	19,5	2	FPM 75	25	2,5	FPM 75
4,1	1,6	FPM 80	9,5	2	FPM 75	14	5	FPM 75	19,5	1	FPM 75	25	3	FPM 75
4,6	2,4	FPM 75	9,5	2,5	FPM 75	14	4	FPM 75	19	6	FPM 75	25	3,5	FPM 75
4	2,5	FPM 75	9,5	3	FPM 75	14	2,5	FPM 75	19,5	3	FPM 75	25	4	FPM 75
4	3	FPM 75	9,92	2,62	FPM 75	14	3	FPM 75	19,99	5,33	FPM 75	25	5	FPM 75
4,34	3,53	FPM 75	9	2	FPM 80	15	2	FPM 75	20	6	FPM 75	25	6	FPM 75
4,48	1,78	FPM 80	9	3	FPM 80	15,6	1,78	FPM 90	20,5	2,5	FPM 75	25,07	2,62	FPM 75
4,47	1,78	FPM 75	10	2	FPM 75	15,54	2,62	FPM 90	20,5	3	FPM 75	25,12	1,78	FPM 75
4	1,5	FPM 75	10	2,5	FPM 75	15,24	5,33	FPM 75	20,5	2,5	FPM 75	25,5	2,5	FPM 75
4	2	FPM 75	10	3	FPM 75	15	4	FPM 75	20,5	2	FPM 75	26,7	1,78	FPM 75
4	2,5	FPM 75	10	3,5	FPM 75	15,08	2,62	FPM 75	20,35	1,78	FPM 75	26	1	FPM 75
4	3	FPM 75	10	4	FPM 75	15	4	FPM 75	20,3	2,4	FPM 90	26	1,5	FPM 75
4,34	3,53	FPM 75	10	5	FPM 75	15,08	2,62	FPM 75	20,3	2,62	FPM 75	26,57	3,53	FPM 75
4,42	2,62	FPM 75	10,5	2	FPM 75	15,24	5,33	FPM 75	20,29	2,62	FPM 75	26,64	2,62	FPM 90
4,5	1	FPM 75	10,5	2,5	FPM 75	15,47	3,53	FPM 75	20,22	3,53	FPM 75	26,59	2,95	FPM 75
5	1,5	FPM 75	10,52	1,83	FPM 75	15,5	1	FPM 75	20	5	FPM 75	26	4	FPM 75
5	1,8	FPM 75	10,69	3,53	FPM 75	15,5	1,5	FPM 75	20	4	FPM 75	26	5	FPM 75
5	2	FPM 75	10,82	1,78	FPM 75	15,5	2	FPM 75	20	2,5	FPM 75	26,34	5,33	FPM 75
5	2,5	FPM 75	10	1,5	FPM 90	15,5	2,5	FPM 75	20,29	2,62	FPM 90	26,5	2	FPM 75
5	3	FPM 75	10,52	1,83	FPM 75	15,5	3	FPM 75	20	1	FPM 75	26,5	2,5	FPM 75
5,28	1,78	FPM 75	10,69	3,53	FPM 75	15,5	4	FPM 75	20	1,5	FPM 75	26,57	3,53	FPM 75
5,5	1	FPM 75	10,82	1,78	FPM 75	15,54	2,62	FPM 75	20	2	FPM 75	26,59	2,95	FPM 75
5,5	1,5	FPM 75	10,77	2,62	FPM 75	15,6	1,78	FPM 75	20	2,65	FPM 80	26,64	2,62	FPM 75
5,5	2	FPM 75	10,82	1,78	FPM 75	15,54	2,62	FPM 90	20	3	FPM 75	26,7	1,78	FPM 75
5,94	3,53	FPM 75	10	1,5	FPM 90	15,6	1,78	FPM 90	20	2,5	FPM 75	26	2,5	FPM 80
5	1	FPM 75	11	1,5	FPM 75	16	1	FPM 75	20	2	FPM 75	26,64	2,62	FPM 90
5,3	2,4	FPM 80	11	2	FPM 75	16	2	FPM 80	21,5	3	FPM 80	27	2,5	FPM 75
5,28	1,78	FPM 75	11	2,5	FPM 75	16	4	FPM 75	21	1	FPM 75	27	1,5	FPM 75
6,5	2,5	FPM 75	11	2,5	FPM 75	16	3	FPM 75	21	1,5	FPM 75	27,94	5,33	FPM 75
6	1,8	FPM 80	11	3	FPM 75	16	2,5	FPM 75	21	2	FPM 75	27,5	2	FPM 75
6,1	1,6	FPM 90	11	4	FPM 75	16	5	FPM 75	21	2,5	FPM 75	27	4	FPM 75
6	1	FPM 75	11,5	2,5	FPM 75	16	5	FPM 75	21	3	FPM 75	27	3,5	FPM 75
6	2	FPM 80	11,5	2,5	FPM 75	16,36	2,21	FPM 75	21	4	FPM 75	27	2,5	FPM 75
6	1,5	FPM 75	11,8	2,4	FPM 75	16,5	2	FPM 75	21	6	FPM 75	27	3	FPM 75
6	2	FPM 75	11,89	1,98	FPM 75	16,5	2,5	FPM 75	21,59	5,33	FPM 75	27	2	FPM 75
6,75	1,78	FPM 75	11,11	1,78	FPM 75	16,81	5,33	FPM 75	21,95	1,78	FPM 75	28	1,5	FPM 75
6	2,5	FPM 75	11,3	2,4	FPM 75	16	2,5	FPM 80	21,92	2,95	FPM 75	28	2	FPM 75
6,5	2	FPM 75	11	2	FPM 90	16	3	FPM 90	21,89	2,62	FPM 75	28	2,5	FPM 75
6,5	1,5	FPM 75	11	1,5	FPM 80	16,3	2,4	FPM 90	21,5	1,5	FPM 75	28	3	FPM 75
6,5	1	FPM 75	11,3	2,4	FPM 75	16	2	FPM 80	21,82	3,53	FPM 75	28	4	FPM 75
6,35	1,78	FPM 75	11,11	1,78	FPM 75	17,5	2,5	FPM 75	22,2	3	FPM 80	28	5	FPM 75
6,07	1,78	FPM 75	11	2	FPM 90	17	1	FPM 80	22,4	3,55	FPM 75	28,17	3,53	FPM 75
6,07	1,63	FPM 75	11,3	2,4	FPM 80	17	4	FPM 75	22	2,62	FPM 80	28,24	2,62	FPM 75
6,02	2,62	FPM 75	12	1	FPM 75	17	2,5	FPM 75	22,4	3,55	FPM 75	28,3	1,78	FPM 75
6	5	FPM 75	12	1,5	FPM 75	17	2	FPM 75	22	3,5	FPM 90	28,5	2	FPM 75
6	4	FPM 75	12	2	FPM 75	17,93	2,46	FPM 75	22	1,5	FPM 75	28,17	3,53	FPM 90
6	3	FPM 75	12	3	FPM 75	17,5	3	FPM 75	22	2,5	FPM 75	28	3	FPM 80
7	1	FPM 75	12	3	FPM 75	17	3	FPM 75	22	3	FPM 75	28	3,5	FPM 80
7	1,5	FPM 75	12	3,5	FPM 75	17	1,5	FPM 75	22	4	FPM 75	29	1,5	FPM 75
7	2	FPM 75	12	4	FPM 75	17,17	1,78	FPM 75	22	5	FPM 75	29	1	FPM 75
7	2,5	FPM 75	12	5	FPM 75	17	5	FPM 75	22,5	2,5	FPM 75	29	4,5	FPM 80
7	3	FPM 75	12,07	5,33	FPM 75	17,93	2,46	FPM 75	22,5	3	FPM 75	29,74	3,53	FPM 75
7	4	FPM 75	12,29	3,53	FPM 75	17	2	FPM 75	23,5	2,5	FPM 75	29,51	5,33	FPM 75
7,5	1,5	FPM 75	12,42	1,78	FPM 75	17	2,5	FPM 75	23	2,5	FPM 75	29,74	2,95	FPM 75
7,5	2	FPM 75	12,42	1,78	FPM 75	18,72	2,62	FPM 75	23,3	2,4	FPM 80	29	2,5	FPM 75

Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM
29,	5,	FPM 75	37,	3,5	FPM 80	45,	4,	FPM 75	54,	3,	FPM 75	64,	5,	FPM 75
29,5	2,	FPM 75	37,47	3,	FPM 75	45,	5,3	FPM 75	54,	4,	FPM 75	64,	4,	FPM 75
29,51	5,33	FPM 75	37,	5,	FPM 75	45,	5,	FPM 75	54,3	5,7	FPM 75	64,	3,	FPM 75
29,74	2,95	FPM 75	37,	1,	FPM 75	45,	6,	FPM 75	55,25	2,62	FPM 75	64,	2,5	FPM 75
29,74	3,53	FPM 75	37,	1,5	FPM 75	45,	3,	FPM 75	55,56	3,53	FPM 80	64,	2,	FPM 75
29,82	2,62	FPM 75	37,	3,	FPM 75	45,	4,	FPM 75	55,56	3,53	FPM 75	64,	1,5	FPM 75
29,87	1,78	FPM 75	37,	3,5	FPM 90	45,	5,	FPM 75	55,5	2,	FPM 75	64,2	5,7	FPM 80
30,	1,	FPM 75	37,	6,	FPM 75	45,	6,	FPM 75	55,	5,	FPM 75	65,	2,5	FPM 75
30,	1,5	FPM 75	37,	4,5	FPM 75	45,69	2,62	FPM 75	55,	4,	FPM 75	65,	5,3	FPM 75
30,	2,	FPM 75	37,	4,	FPM 75	45,69	2,62	FPM 80	55,	3,5	FPM 75	65,	1,5	FPM 75
30,	2,5	FPM 75	38,	4,5	FPM 75	45,	5,3	FPM 75	55,	3,5	FPM 75	65,	2,	FPM 75
30,	3,	FPM 75	38,	5,	FPM 75	45,	3,5	FPM 80	55,	2,5	FPM 75	65,	2,5	FPM 75
30,	4,	FPM 75	38,	2,	FPM 75	46,	6,	FPM 75	55,	1,5	FPM 75	65,	3,	FPM 75
30,8	3,6	FPM 90	38,	2,5	FPM 75	46,	1,5	FPM 75	55,	3,	FPM 75	65,	4,	FPM 75
30,	5,	FPM 75	38,	3,	FPM 75	46,99	5,33	FPM 75	55,3	5,7	FPM 75	65,	5,	FPM 75
30,	5,	FPM 80	38,	3,5	FPM 75	46,	2,5	FPM 75	55,	2,5	FPM 75	65,	3,	FPM 80
30,	6,	FPM 75	38,	4,	FPM 75	46,	3,	FPM 75	55,	1,5	FPM 75	66,	4,	FPM 75
31,	1,5	FPM 75	38,	4,5	FPM 75	46,	2,	FPM 75	56,82	2,62	FPM 75	66,35	2,62	FPM 75
31,34	3,53	FPM 90	38,	5,	FPM 75	47,29	2,62	FPM 75	56,87	1,78	FPM 75	66,	3,5	FPM 75
31,12	5,33	FPM 75	38,	6,	FPM 75	47,	5,	FPM 75	56,82	2,62	FPM 75	66,5	2,5	FPM 75
31,47	1,78	FPM 75	38,	2,5	FPM 80	47,22	3,53	FPM 75	56,74	3,53	FPM 75	66,4	1,78	FPM 75
31,	2,5	FPM 75	38,	1,5	FPM 75	47,22	3,53	FPM 75	56,52	5,33	FPM 75	66,34	2,62	FPM 75
31,	4,	FPM 75	39,	2,5	FPM 75	47,	2,5	FPM 75	56,	2,5	FPM 75	66,27	3,53	FPM 75
31,	4,5	FPM 75	39,	4,5	FPM 80	47,35	1,78	FPM 75	56,	2,	FPM 75	66,27	3,53	FPM 75
31,	4,5	FPM 80	39,34	2,62	FPM 75	47,	5,	FPM 75	56,	3,	FPM 75	66,04	5,33	FPM 75
31,	5,	FPM 75	39,	4,5	FPM 75	47,22	3,53	FPM 75	56,87	1,78	FPM 90	66,	3,	FPM 75
31,12	5,33	FPM 75	39,	3,	FPM 75	47,22	3,53	FPM 75	57,	5,	FPM 75	66,	5,	FPM 75
31,34	3,53	FPM 75	39,	2,	FPM 75	47,29	2,62	FPM 75	57,	1,5	FPM 75	66,	2,	FPM 75
31,42	2,62	FPM 75	39,	5,	FPM 75	47,35	1,78	FPM 75	57,	2,	FPM 75	66,	3,5	FPM 75
31,47	1,78	FPM 75	39,	3,5	FPM 75	48,	3,	FPM 80	57,	2,	FPM 75	67,	1,5	FPM 75
31,5	2,	FPM 75	40,	6,	FPM 80	48,	1,5	FPM 75	57,	2,5	FPM 75	67,	2,5	FPM 75
32,92	3,53	FPM 75	40,	2,5	FPM 90	48,	2,5	FPM 75	57,	4,	FPM 75	67,	4,	FPM 75
32,	2,2	FPM 75	40,	3,	FPM 75	48,	3,	FPM 75	57,	3,	FPM 75	67,	5,	FPM 75
32,99	2,62	FPM 75	40,	2,	FPM 80	48,	3,5	FPM 75	57,	3,	FPM 75	67,95	2,62	FPM 75
32,69	5,33	FPM 75	40,	6,	FPM 80	48,	4,	FPM 75	58,	2,	FPM 75	67,84	3,53	FPM 80
32,	6,	FPM 75	40,	1,5	FPM 75	48,	6,	FPM 75	58,	4,	FPM 75	68,	1,5	FPM 75
32,	5,	FPM 75	40,87	3,53	FPM 75	48,9	2,62	FPM 75	58,	6,	FPM 75	68,	2,	FPM 75
32,	4,	FPM 75	40,	6,	FPM 75	48,	2,	FPM 80	58,	4,	FPM 75	68,	2,5	FPM 75
32,	2,	FPM 75	40,	5,	FPM 75	48,	2,	FPM 75	58,	3,	FPM 75	68,	3,	FPM 75
32,	2,5	FPM 75	40,87	3,53	FPM 75	49,	3,	FPM 75	58,	2,	FPM 75	68,	4,	FPM 75
32,92	3,53	FPM 75	40,	4,	FPM 75	49,2	5,7	FPM 75	58,	1,5	FPM 75	68,	5,	FPM 75
32,99	2,62	FPM 75	40,	4,	FPM 75	49,6	5,7	FPM 75	59,	3,	FPM 75	69,	1,5	FPM 75
33,	2,5	FPM 75	40,	2,5	FPM 75	49,	2,	FPM 75	59,99	2,62	FPM 75	69,	2,	FPM 75
33,	1,5	FPM 75	40,	2,	FPM 75	49,	1,5	FPM 75	59,92	3,53	FPM 75	69,	2,5	FPM 75
33,	2,	FPM 75	40,	2,5	FPM 80	49,6	5,7	FPM 75	59,92	3,53	FPM 75	69,	3,	FPM 75
33,	3,	FPM 75	40,	2,5	FPM 75	49,2	5,7	FPM 75	59,69	5,33	FPM 75	69,	4,	FPM 75
33,	4,	FPM 75	40,	3,	FPM 75	50,47	2,62	FPM 80	59,5	2,	FPM 75	69,	5,	FPM 75
33,05	1,78	FPM 75	40,64	5,33	FPM 75	50,17	3,53	FPM 80	59,36	3,	FPM 75	69,	6,	FPM 75
33,5	2,	FPM 75	41,	4,	FPM 75	50,	1,5	FPM 80	59,	5,	FPM 75	69,22	5,33	FPM 75
34,29	5,33	FPM 75	41,	2,5	FPM 75	50,	1,5	FPM 75	59,	1,5	FPM 75	69,3	5,7	FPM 75
34,	4,5	FPM 75	41,	3,	FPM 75	50,	2,	FPM 75	59,2	5,7	FPM 80	69,44	3,53	FPM 75
34,	3,5	FPM 80	41,	4,5	FPM 75	50,	2,5	FPM 75	59,	2,5	FPM 75	69,5	2,	FPM 75
34,65	1,78	FPM 75	41,	2,5	FPM 75	50,	3,	FPM 75	59,	2,	FPM 75	69,52	2,62	FPM 75
34,59	2,62	FPM 75	41,	1,78	FPM 75	50,	3,5	FPM 75	60,	3,	FPM 75	69,57	1,78	FPM 75
34,52	3,53	FPM 75	41,	1,5	FPM 75	50,	4,	FPM 75	60,04	1,78	FPM 75	69,3	5,7	FPM 80
34,5	4,5	FPM 75	41,	1,	FPM 75	50,	5,	FPM 75	60,	3,	FPM 75	69,52	2,62	FPM 80
34,	2,	FPM 75	41,	2,	FPM 75	50,17	5,33	FPM 75	60,	2,	FPM 75	70,	2,	FPM 75
34,	3,	FPM 75	42,52	2,62	FPM 75	50,39	3,53	FPM 75	60,	2,5	FPM 75	70,	2,5	FPM 75
34,42	2,95	FPM 75	42,86	3,53	FPM 75	50,47	2,62	FPM 75	60,	3,	FPM 75	70,	3,	FPM 75
34,	1,5	FPM 75	42,	5,	FPM 75	50,52	1,78	FPM 75	60,	4,	FPM 75	70,	5,	FPM 75
34,	3,5	FPM 80	42,	4,	FPM 75	51,	3,	FPM 75	60,	6,	FPM 75	70,5	2,	FPM 75
34,	4,5	FPM 75	42,	3,	FPM 75	51,5	1,5	FPM 75	60,04	1,78	FPM 75	70,	6,	FPM 80
35,	1,5	FPM 80	42,	1,5	FPM 75	51,	2,5	FPM 75	61,	1,5	FPM 75	71,	1,5	FPM 75
35,	5,	FPM 75	42,	1,	FPM 75	51,	2,	FPM 75	61,	2,	FPM 75	71,	2,	FPM 75
35,	4,	FPM 75	42,	2,5	FPM 80	51,5	1,5	FPM 75	61,	2,5	FPM 75	71,	2,5	FPM 75
35,	5,	FPM 80	42,	2,	FPM 75	52,	1,	FPM 75	61,	3,	FPM 75	71,	3,	FPM 75
35,	3,	FPM 75	43,	3,	FPM 75	52,	1,5	FPM 75	61,	4,	FPM 75	71,	4,	FPM 75
35,	2,5	FPM 75	43,	4,	FPM 75	52,	2,	FPM 75	61,	5,	FPM 75	71,	5,	FPM 75
35,	1,5	FPM 75	43,	4,5	FPM 75	52,	2,5	FPM 75	61,6	2,62	FPM 75	71,12	2,62	FPM 75
35,	2,5	FPM 75	43,	5,	FPM 75	52,	3,	FPM 75	62,	2,5	FPM 75	72,	1,5	FPM 75
35,	2,	FPM 75	43,69	3,	FPM 75	52,	4,	FPM 75	62,	1,5	FPM 75	72,	2,	FPM 75
36,	3,	FPM 75	43,	2,	FPM 75	52,	6,	FPM 75	62,	2,	FPM 75	72,	2,5	FPM 75
36,	4,5	FPM 80	43,	5,	FPM 75	52,07	2,62	FPM 75	62,87	5,33	FPM 75	72,	3,	FPM 75
36,17	2,62	FPM 75	43,	4,5	FPM 75	53,	1,5	FPM 75	62,87	5,33	FPM 75	72,	4,	FPM 75
36,09	3,53	FPM 75	43,	4,	FPM 75	53,	5,	FPM 80	62,	5,	FPM 75	72,	5,	FPM 75
36,	5,	FPM 75	43,	3,	FPM 75	53,7	1,78	FPM 75	62,	3,	FPM 75	72,	6,	FPM 75
36,	4,5	FPM 75	44,	1,5	FPM 75	53,64	2,62	FPM 75	62,87	5,33	FPM 75	72,39	5,33	FPM 75
36,	4,	FPM 75	44,	2,	FPM 75	53,57	3,53	FPM 75	63,	1,5	FPM 75	72,62	3,53	FPM 75
36,	1,5	FPM 75	44,	2,5	FPM 75	53,34	5,33	FPM 75	63,	2,	FPM 75	72,69	2,62	FPM 75
36,	2,	FPM 75	44,	2,5	FPM 75	53,	4,	FPM 75	63,	5,	FPM 80	72,75	1,78	FPM 75
36,17	2,62	FPM 75	44,	3,	FPM 75	53,09	3,	FPM 75	63,	2,5	FPM 75	72,76	1,78	FPM 90
36,	4,5	FPM 80	44,	4,	FPM 75	53,	2,	FPM 75	63,	3,	FPM 75	73,	2,	FPM 75
37,	2,	FPM 75	44,	4,5	FPM 75	53,	3,	FPM 75	63,	5,	FPM 75	73,	2,5	FPM 75
37,82	1,78	FPM 75	44,	5,	FPM 75	53,	2,5	FPM 75	63,09	3,53	FPM 75	73,	3,	FPM 75
37,77	2,62	FPM 75	44,04	3,53	FPM 75	54,	1,5	FPM 75	63,17	2,62	FPM 75	73,	4,	FPM 75
37,69	3,53	FPM 75	44,12	2,62	FPM 75	54,2	5,7	FPM 80	63,22	1,78	FPM 75	73,	5,	FPM 75
37,5	2,	FPM 75	44,17	1,78	FPM 75	54,	2,	FPM 75	64,2	5,7	FPM 75	74,	2,	FPM 75
37,47	5,33	FPM 75	44,	2,5	FPM 80	54,	2,5	FPM 75	64,77	2,62	FPM 75	74,	3,	FPM 75

Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM
74,	5,	FPM 75	86,	5,	FPM 75	100,	1,5	FPM 75	124,6	5,7	FPM 80	154,5	8,4	FPM 75
74,3	5,7	FPM 75	86,	6,	FPM 75	100,	2,	FPM 75	125,	2,	FPM 75	154,	3,	FPM 75
74,5	2,	FPM 75	86,	3,	FPM 80	100,	2,5	FPM 75	125,	2,5	FPM 75	155,	3,	FPM 75
74,6	3,53	FPM 75	87,	1,5	FPM 75	100,	3,	FPM 75	125,	3,	FPM 75	155,	4,	FPM 75
74,2	5,7	FPM 80	87,	2,	FPM 75	100,	4,	FPM 75	125,	4,	FPM 75	155,	5,	FPM 75
74,4	3,1	FPM 90	87,	2,5	FPM 75	100,	4,5	FPM 75	125,	5,	FPM 75	155,	6,	FPM 75
74,	3,5	FPM 75	87,	3,	FPM 75	100,	5,	FPM 75	126,	4,5	FPM 75	155,	5,	FPM 80
74,	3,	FPM 75	87,	4,	FPM 75	100,	6,	FPM 75	126,59	3,53	FPM 75	155,	4,5	FPM 75
74,	3,	FPM 80	87,	3,	FPM 80	100,97	5,33	FPM 75	126,67	2,62	FPM 75	155,	6,	FPM 80
74,	3,5	FPM 80	88,	1,5	FPM 75	100,97	6,99	FPM 75	126,37	5,33	FPM 75	158,12	5,33	FPM 75
74,6	3,53	FPM 80	88,	2,	FPM 75	101,19	3,53	FPM 75	126,37	6,99	FPM 75	158,12	6,99	FPM 75
75,	3,	FPM 75	88,	3,	FPM 75	101,27	2,62	FPM 75	126,72	1,78	FPM 75	158,34	3,53	FPM 75
75,	4,	FPM 75	88,	4,	FPM 75	101,32	1,78	FPM 75	126,67	2,62	FPM 75	158,42	2,62	FPM 75
75,57	5,33	FPM 75	88,	5,	FPM 75	102,	2,5	FPM 75	128,	2,	FPM 75	158,35	3,53	FPM 80
75,79	3,53	FPM 75	88,27	5,33	FPM 75	103,	2,	FPM 75	128,	2,5	FPM 75	159,3	5,7	FPM 75
75,87	2,62	FPM 75	88,49	3,53	FPM 75	103,	3,5	FPM 75	129,3	5,7	FPM 75	159,3	5,7	FPM 80
75,92	1,78	FPM 75	88,49	3,53	FPM 75	103,	6,	FPM 75	129,54	5,33	FPM 75	160,	2,	FPM 75
75,	3,5	FPM 80	88,57	2,62	FPM 75	104,14	5,33	FPM 75	129,54	6,99	FPM 75	160,	2,5	FPM 75
75,	5,5	FPM 80	88,62	1,78	FPM 75	104,37	3,53	FPM 75	129,77	3,53	FPM 75	160,	3,	FPM 75
76,	1,5	FPM 75	89,	1,5	FPM 75	104,37	3,53	FPM 75	130,	2,	FPM 75	160,	4,	FPM 75
76,	2,	FPM 75	89,	2,	FPM 75	104,2	5,7	FPM 80	130,	2,5	FPM 75	160,	5,	FPM 75
76,	3,	FPM 75	89,	2,5	FPM 75	105,	2,	FPM 75	130,	3,	FPM 75	160,	6,	FPM 75
76,	4,	FPM 75	89,	5,	FPM 75	105,	2,5	FPM 75	130,	4,	FPM 75	160,	5,3	FPM 75
76,	6,	FPM 75	89,3	5,7	FPM 75	105,	3,	FPM 75	130,	5,	FPM 75	164,47	5,33	FPM 75
77,	1,5	FPM 75	89,2	5,7	FPM 80	105,	4,	FPM 75	130,	6,	FPM 75	164,47	6,99	FPM 75
77,	3,	FPM 75	89,69	5,33	FPM 80	105,	5,	FPM 75	132,	2,	FPM 75	164,69	3,53	FPM 75
77,	4,	FPM 75	90,	1,5	FPM 75	105,	6,	FPM 75	132,72	5,33	FPM 75	164,77	2,62	FPM 75
78,	1,5	FPM 75	90,	2,	FPM 75	106,	2,	FPM 75	132,72	6,99	FPM 75	165,	2,	FPM 75
78,	2,	FPM 75	90,	2,5	FPM 75	106,	2,5	FPM 75	132,94	3,53	FPM 75	165,	2,5	FPM 75
78,	2,5	FPM 75	90,	3,	FPM 75	107,32	5,33	FPM 75	133,02	2,62	FPM 75	165,	3,	FPM 75
78,	3,	FPM 75	90,	4,	FPM 75	107,54	3,53	FPM 75	133,07	1,78	FPM 75	165,	4,	FPM 75
78,	4,	FPM 75	90,	4,5	FPM 75	107,62	2,62	FPM 75	134,3	5,7	FPM 75	165,	4,5	FPM 75
78,74	5,33	FPM 75	90,	5,	FPM 75	107,67	1,78	FPM 75	134,1	8,4	FPM 75	165,	5,	FPM 75
78,97	3,53	FPM 75	90,	5,3	FPM 80	109,3	5,7	FPM 75	135,	2,	FPM 75	165,	6,	FPM 75
78,74	6,99	FPM 75	91,	3,	FPM 75	109,2	5,7	FPM 80	135,	2,5	FPM 75	167,	3,	FPM 75
79,	1,5	FPM 75	91,	5,	FPM 75	109,6	5,7	FPM 75	135,	3,	FPM 75	168,	3,	FPM 75
79,	2,5	FPM 75	91,44	5,33	FPM 75	110,	2,	FPM 75	135,	4,	FPM 75	169,3	5,7	FPM 75
79,	3,	FPM 75	91,44	5,33	FPM 75	110,	2,5	FPM 75	135,	5,	FPM 75	169,2	5,7	FPM 80
79,	4,	FPM 75	91,67	3,53	FPM 75	110,	3,	FPM 75	135,89	5,33	FPM 75	170,	3,	FPM 75
79,3	5,7	FPM 75	91,67	3,53	FPM 75	110,	4,	FPM 75	135,89	6,99	FPM 75	170,	4,	FPM 75
80,	1,5	FPM 75	91,67	3,53	FPM 80	110,	5,	FPM 75	135,89	6,99	FPM 80	170,	5,	FPM 75
80,	2,	FPM 75	92,	1,5	FPM 75	110,49	5,33	FPM 75	136,12	3,53	FPM 75	170,82	5,33	FPM 75
80,	2,5	FPM 75	92,	2,5	FPM 75	110,72	3,53	FPM 75	139,07	5,33	FPM 75	170,82	6,99	FPM 75
80,	3,	FPM 75	92,	3,	FPM 75	110,	6,	FPM 80	139,07	6,99	FPM 75	170,	5,	FPM 80
80,	4,	FPM 75	92,	4,	FPM 75	112,	4,	FPM 75	139,29	3,53	FPM 75	171,	3,	FPM 75
80,	5,	FPM 75	92,	3,	FPM 80	113,	3,	FPM 75	139,3	5,7	FPM 75	171,04	3,53	FPM 75
80,	6,	FPM 75	93,	2,	FPM 75	113,67	5,33	FPM 75	139,37	2,62	FPM 75	171,05	3,53	FPM 75
80,	5,3	FPM 80	93,	2,5	FPM 75	113,67	6,99	FPM 75	139,2	5,7	FPM 80	171,12	2,62	FPM 75
80,	5,3	FPM 80	94,	1,5	FPM 75	113,89	3,53	FPM 75	140,	2,	FPM 75	172,	3,	FPM 75
81,	1,5	FPM 75	94,	2,	FPM 75	113,97	2,62	FPM 75	140,	2,5	FPM 75	175,	2,	FPM 75
81,	4,	FPM 75	94,	2,5	FPM 75	113,98	2,62	FPM 75	140,	3,	FPM 75	175,	3,	FPM 75
81,92	5,33	FPM 75	94,	3,	FPM 75	114,02	1,78	FPM 75	140,	3,5	FPM 75	175,	4,	FPM 75
81,92	5,33	FPM 80	94,	4,	FPM 75	114,3	5,7	FPM 75	140,	4,	FPM 75	175,	5,	FPM 75
82,	1,5	FPM 75	94,	5,	FPM 75	114,6	5,7	FPM 80	140,	5,	FPM 75	175,	6,	FPM 80
82,	2,	FPM 75	94,62	5,33	FPM 75	115,	2,	FPM 75	140,	6,	FPM 75	176,	2,	FPM 75
82,	3,	FPM 75	94,84	3,53	FPM 75	115,	2,5	FPM 75	142,24	5,33	FPM 75	177,17	5,33	FPM 75
82,	4,	FPM 75	94,92	2,62	FPM 75	115,	3,	FPM 75	142,24	6,99	FPM 75	177,17	6,99	FPM 75
82,	5,	FPM 75	94,97	1,78	FPM 75	115,	4,	FPM 75	142,47	3,53	FPM 75	177,39	3,53	FPM 75
82,14	3,53	FPM 75	95,	1,5	FPM 75	115,	4,5	FPM 75	142,47	3,53	FPM 90	177,47	2,62	FPM 75
82,22	2,62	FPM 75	95,	2,	FPM 75	115,	5,	FPM 75	142,	6,	FPM 80	178,	3,	FPM 75
82,27	1,78	FPM 75	95,	2,5	FPM 75	116,84	5,33	FPM 75	144,3	5,7	FPM 75	179,	3,	FPM 75
82,22	2,62	FPM 80	95,	4,	FPM 75	116,84	6,99	FPM 75	144,1	8,4	FPM 75	179,2	5,7	FPM 80
83,	1,5	FPM 75	95,	5,	FPM 75	117,	4,	FPM 75	145,	2,5	FPM 75	179,	4,5	FPM 75
83,	2,5	FPM 75	95,	6,	FPM 75	117,07	3,53	FPM 75	145,	4,	FPM 75	180,	3,5	FPM 75
83,	3,	FPM 75	96,	1,5	FPM 75	118,	3,	FPM 80	145,42	5,33	FPM 75	180,	4,	FPM 75
83,	5,	FPM 75	96,	2,5	FPM 75	118,	4,5	FPM 75	145,42	6,99	FPM 75	180,	5,	FPM 75
84,	1,5	FPM 75	96,	3,	FPM 75	119,3	5,7	FPM 75	145,64	3,53	FPM 75	180,	6,	FPM 75
84,	2,	FPM 75	97,	2,	FPM 75	119,5	2,	FPM 75	145,72	2,62	FPM 75	183,52	5,33	FPM 75
84,	2,5	FPM 75	97,	3,	FPM 75	119,4	3,1	FPM 90	147,	4,	FPM 75	183,52	6,99	FPM 75
84,	4,	FPM 75	97,	4,	FPM 75	119,3	5,7	FPM 80	148,	2,	FPM 75	183,74	3,53	FPM 75
84,	5,	FPM 75	97,	5,	FPM 75	119,5	3,	FPM 80	148,	2,5	FPM 75	183,82	2,62	FPM 75
84,1	5,7	FPM 75	97,79	5,33	FPM 75	120,	2,	FPM 75	148,	3,	FPM 75	183,52	6,99	FPM 80
84,6	5,7	FPM 75	97,	3,5	FPM 75	120,	2,5	FPM 75	148,59	5,33	FPM 75	184,3	5,7	FPM 75
85,	2,	FPM 75	98,	1,5	FPM 75	120,	3,	FPM 75	148,59	6,99	FPM 75	184,3	5,7	FPM 75
85,	2,5	FPM 75	98,	2,	FPM 75	120,	4,	FPM 75	148,82	3,53	FPM 75	184,1	8,4	FPM 75
85,	3,	FPM 75	98,	2,5	FPM 75	120,	6,	FPM 75	149,3	5,7	FPM 75	185,	2,5	FPM 75
85,	4,	FPM 75	98,	3,	FPM 75	120,02	5,33	FPM 75	149,5	2,	FPM 75	185,	3,	FPM 75
85,	5,	FPM 75	98,	4,	FPM 75	120,02	6,99	FPM 75	150,	2,5	FPM 75	185,	4,	FPM 75
85,	6,	FPM 75	98,	5,	FPM 75	120,24	3,53	FPM 75	150,	3,	FPM 75	185,	5,	FPM 75
85,09	5,33	FPM 75	98,5	3,	FPM 75	120,32	2,62	FPM 75	150,	4,	FPM 75	185,	6,	FPM 75
85,32	3,53	FPM 75	98,02	3,53	FPM 75	120,37	1,78	FPM 75	150,	5,	FPM 75	187,	3,5	FPM 75
85,	6,	FPM 80	98,02	3,53	FPM 80	120,33	2,62	FPM 75	150,	6,	FPM 75	189,3	5,7	FPM 75
85,	4,5	FPM 80	99,	2,	FPM 75	120,	6,	FPM 80	150,	5,	FPM 80	189,87	5,33	FPM 75
86,	1,5	FPM 75	99,	2,5	FPM 75	123,19	5,33	FPM 75	151,77	5,33	FPM 75	189,87	6,99	FPM 75
86,	2,	FPM 75	99,	3,	FPM 75	123,19	6,99	FPM 75	151,77	6,99	FPM 75	189,3	5,7	FPM 80
86,	2,5	FPM 75	99,	4,	FPM 75	123,42	3,53	FPM 75	151,99	3,53	FPM 75	189,5	8,4	FPM 75
86,	3,	FPM 75	99,2	5,7	FPM 80	124,3	5,7	FPM 75	152,07	2,62	FPM 75	190,	3,	FPM 75
86,	4,	FPM 75	99,	4,5	FPM 75	124,3	5,7	FPM 75	153,	2,	FPM 75	190,	4,	FPM 75

Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM	Ø d1	Ø d2	FPM
190,	5,	FPM 75	221,62	5,33	FPM 75	266,07	5,33	FPM 75	340,	4,	FPM 75	430,66	6,99	FPM 75
190,	6,	FPM 75	221,84	3,53	FPM 75	266,07	6,99	FPM 75	340,	5,	FPM 75	435,	4,	FPM 75
190,09	3,53	FPM 75	221,92	2,62	FPM 75	266,29	3,53	FPM 75	342,27	6,99	FPM 75	435,	5,	FPM 75
190,17	2,62	FPM 75	225,	3,	FPM 75	270,	3,	FPM 75	345,	4,	FPM 75	440,	4,	FPM 75
190,1	3,53	FPM 75	225,	4,	FPM 75	270,	4,	FPM 75	345,	5,	FPM 75	440,	5,	FPM 75
190,1	3,53	FPM 80	225,	5,	FPM 75	270,	5,	FPM 75	345,	7,	FPM 75	443,36	6,99	FPM 75
192,	5,	FPM 75	227,97	5,33	FPM 75	275,	4,	FPM 75	350,	4,	FPM 75	445,	5,	FPM 75
194,	2,	FPM 75	227,97	6,99	FPM 75	275,	5,	FPM 75	350,	5,	FPM 75	450,	4,	FPM 75
194,	2,5	FPM 75	227,	4,5	FPM 75	275,	2,5	FPM 75	350,	6,	FPM 75	450,	5,	FPM 75
194,3	5,7	FPM 75	227,97	6,99	FPM 80	278,77	5,33	FPM 75	354,97	5,33	FPM 75	455,	4,	FPM 75
195,	3,	FPM 75	228,19	3,53	FPM 75	278,77	6,99	FPM 75	354,97	6,99	FPM 75	455,	5,	FPM 75
195,	4,	FPM 75	228,27	2,62	FPM 75	278,99	3,53	FPM 75	355,	4,	FPM 75	456,06	3,53	FPM 75
195,	5,	FPM 75	229,5	8,4	FPM 80	280,	3,	FPM 75	355,	5,	FPM 75	456,06	6,99	FPM 75
195,	6,	FPM 75	229,1	8,4	FPM 75	280,	4,	FPM 75	355,19	3,53	FPM 75	460,	4,	FPM 75
195,	6,	FPM 80	230,	2,5	FPM 75	280,	5,	FPM 75	359,3	5,7	FPM 75	460,	5,	FPM 75
196,22	5,33	FPM 75	230,	3,	FPM 75	285,	3,	FPM 75	360,	4,	FPM 75	465,	4,	FPM 75
196,22	6,99	FPM 75	230,	4,	FPM 75	285,	4,	FPM 75	360,	5,	FPM 75	465,	5,	FPM 75
196,44	3,53	FPM 75	230,	5,	FPM 75	285,	5,	FPM 75	365,	4,	FPM 75	468,76	6,99	FPM 75
196,52	2,62	FPM 75	233,	3,	FPM 75	285,	5,	FPM 80	365,	5,	FPM 75	470,	5,	FPM 75
199,3	5,7	FPM 75	234,32	5,33	FPM 75	289,5	8,4	FPM 75	365,	6,	FPM 75	475,	4,	FPM 75
199,3	5,7	FPM 80	234,32	6,99	FPM 75	289,3	5,7	FPM 75	367,67	6,99	FPM 75	475,	5,	FPM 75
199,5	8,4	FPM 80	234,54	3,53	FPM 75	290,	3,	FPM 75	369,3	5,7	FPM 80	480,	4,	FPM 75
199,3	5,7	FPM 90	234,62	2,62	FPM 75	290,	4,	FPM 75	370,	4,	FPM 75	480,	5,	FPM 75
200,	3,	FPM 75	235,	3,	FPM 75	290,	5,	FPM 75	370,	5,	FPM 75	481,41	5,33	FPM 75
200,	4,	FPM 75	235,	4,	FPM 75	291,47	5,33	FPM 75	373,	7,	FPM 75	481,46	6,99	FPM 75
200,	5,	FPM 75	235,	5,	FPM 75	291,47	6,99	FPM 75	375,	4,	FPM 75	485,	4,	FPM 75
202,57	5,33	FPM 75	239,3	5,7	FPM 75	291,69	3,53	FPM 75	375,	5,	FPM 75	485,	5,	FPM 75
202,57	6,99	FPM 75	239,5	8,4	FPM 80	294,5	8,4	FPM 75	375,	6,	FPM 75	490,	4,	FPM 75
202,79	3,53	FPM 75	240,	3,	FPM 75	295,	4,	FPM 75	379,5	8,4	FPM 75	490,	5,	FPM 75
202,87	2,62	FPM 75	240,	4,	FPM 75	295,	5,	FPM 75	379,3	5,7	FPM 80	494,16	6,99	FPM 75
203,	6,	FPM 80	240,	5,	FPM 75	297,	4,	FPM 75	380,	4,	FPM 75	495,	5,	FPM 75
204,	5,	FPM 75	240,67	5,33	FPM 75	299,5	8,4	FPM 80	380,	5,	FPM 75	500,	4,	FPM 75
204,2	5,7	FPM 75	240,67	6,99	FPM 75	300,	3,	FPM 75	380,37	5,33	FPM 75	500,	5,	FPM 75
205,	2,	FPM 75	240,89	3,53	FPM 75	300,	4,	FPM 75	380,37	6,99	FPM 75	505,	5,	FPM 75
205,	3,	FPM 75	240,97	2,62	FPM 75	300,	5,	FPM 75	380,59	3,53	FPM 75	506,81	5,33	FPM 75
205,	4,	FPM 75	240,89	3,53	FPM 90	300,	6,	FPM 75	385,	4,	FPM 75	506,86	6,99	FPM 75
205,	5,	FPM 75	244,	2,	FPM 75	304,17	5,33	FPM 75	385,	5,	FPM 75	510,	5,	FPM 75
205,	6,	FPM 75	244,5	8,4	FPM 75	304,17	6,99	FPM 75	390,	4,	FPM 75	515,	5,	FPM 75
208,92	5,33	FPM 75	245,	3,	FPM 75	304,39	3,59	FPM 75	390,	5,	FPM 75	520,	4,	FPM 75
209,14	3,53	FPM 75	245,	4,	FPM 75	305,	3,	FPM 75	393,07	6,99	FPM 75	525,	4,	FPM 75
209,22	2,62	FPM 75	245,	5,	FPM 75	305,	4,	FPM 75	394,	6,	FPM 75	525,	5,	FPM 75
209,1	8,4	FPM 75	247,02	5,33	FPM 75	305,	5,	FPM 75	395,	4,	FPM 75	530,	5,	FPM 75
210,	3,	FPM 75	247,26	3,53	FPM 75	310,	3,	FPM 75	395,	5,	FPM 75	532,21	5,33	FPM 75
210,	4,	FPM 75	247,32	2,62	FPM 75	310,	4,	FPM 75	400,	4,	FPM 75	532,26	6,99	FPM 75
210,	5,	FPM 75	249,3	5,7	FPM 75	315,	3,	FPM 75	400,	5,	FPM 75	540,	5,	FPM 75
210,	6,	FPM 75	250,	3,	FPM 75	315,	4,	FPM 75	405,	4,	FPM 75	545,	4,	FPM 75
211,	2,5	FPM 75	250,	4,	FPM 75	315,	5,	FPM 75	405,	5,	FPM 75	545,	5,	FPM 75
211,	3,	FPM 75	250,	5,	FPM 75	316,87	6,99	FPM 75	405,26	3,53	FPM 75	550,	4,	FPM 75
214,3	5,7	FPM 75	250,	6,	FPM 75	319,3	5,7	FPM 75	405,26	5,33	FPM 75	555,	5,	FPM 75
214,3	5,7	FPM 80	253,37	5,33	FPM 75	319,5	8,4	FPM 75	405,26	6,99	FPM 75	557,61	5,33	FPM 75
215,	2,	FPM 75	253,37	6,99	FPM 75	319,5	8,4	FPM 80	410,	4,	FPM 75	557,66	6,99	FPM 75
215,	4,	FPM 75	253,59	3,53	FPM 75	319,3	5,7	FPM 75	410,	5,	FPM 75	560,	4,	FPM 75
215,	4,5	FPM 75	254,3	5,7	FPM 75	319,3	5,7	FPM 80	410,	8,	FPM 80	560,	5,	FPM 75
215,	5,	FPM 75	255,	3,	FPM 75	320,	4,	FPM 75	415,	4,	FPM 75	565,	4,	FPM 75
215,27	5,33	FPM 75	255,	4,	FPM 75	320,	5,	FPM 75	415,	5,	FPM 75	570,	5,	FPM 75
215,27	6,99	FPM 75	255,	5,	FPM 75	325,	4,	FPM 75	417,96	6,99	FPM 75	582,68	5,33	FPM 75
215,49	3,53	FPM 75	258,	6,	FPM 80	325,	5,	FPM 75	419,3	5,7	FPM 75	582,68	6,99	FPM 75
215,57	2,62	FPM 75	259,5	8,4	FPM 75	325,	6,	FPM 75	420,	4,	FPM 75	585,	4,	FPM 75
219,3	5,7	FPM 75	259,1	8,4	FPM 80	329,57	5,33	FPM 75	420,	5,	FPM 75	595,	5,	FPM 75
219,5	8,4	FPM 80	259,3	5,7	FPM 80	329,57	6,99	FPM 75	425,	4,	FPM 75	608,08	5,33	FPM 75
220,	2,	FPM 75	260,	3,	FPM 75	329,79	3,53	FPM 75	425,	5,	FPM 75	608,08	6,99	FPM 75
220,	3,	FPM 75	260,	4,	FPM 75	330,	4,	FPM 75	430,	4,	FPM 75	633,48	5,33	FPM 75
220,	4,	FPM 75	260,	5,	FPM 75	330,	5,	FPM 75	430,	5,	FPM 75	633,48	6,99	FPM 75
220,	5,	FPM 75	265,	4,	FPM 75	335,	4,	FPM 75	430,66	3,53	FPM 75	658,88	5,33	FPM 75
220,	6,	FPM 75	265,	5,	FPM 75	335,	5,	FPM 75	430,66	5,33	FPM 75	658,88	6,99	FPM 75

